

0481 SAFETY GLOW INSIDE RELEASE HANDLE



- Glow-in-the-dark knob
- ADA Compliant

Specifications

Material

Steel rod and flange; Safety-Glow™ plastic knob

Finish

Kasonized (Zinc plated)

Mounting

Holes drilled for No. 10 (5.0 mm) screws

Packaging

24 per carton

Weight

Approx. 20 lb (9.1 kg) per carton

Temperature Range

-40°F to 150°F (-40°C to 65°C)

INSTALLATION INSTRUCTIONS

0481 Safety Glow Inside Release Handle 0482 Hi-Temp Inside Release Push Handle 0487 Frost-Free Inside Release Push Handle

1. Drill a 3/4" diameter (19.1 mm) hole through the door from the warm side at the location of latch inside release hole. Hole must be square to door surface for proper alignment and operation. For rods using a cross pin, drill a 1" diameter (25.4 mm) x 2" deep pocket from the cold side to accommodate pin and washers.
2. Mount to the door using (3) #10 (5.0mm) round head screws.
For Freezers, fill warm side of cavity with low temperature grease to limit air infiltration and ice formation through hole.
3. Test to assure latch release function.
WARNING: Function is critical. Entrapment in freezer can cause severe injury or death.

Fig. 1

